

## 0.3 OD M37.0 x 0.75, Mounted Absorptive ND Filter



Stock **#59-165** 3-5 DAYS

- 1 +

**A\$68.80**

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-9                       |
| A\$68.80                      |
| Qty 10+                       |
| A\$64.96                      |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

### Get Product Downloads

**Optical Density OD (Average):**  
0.3

**Clear Aperture CA (mm):**  
31.9

**Filter Thread:**  
M37 x0.75

**Substrate:** ☐  
ND Filter Glass

|                                                                       |
|-----------------------------------------------------------------------|
| <b>Thickness with Mount (mm):</b><br>4.50                             |
| <b>Surface Quality:</b><br>80-50                                      |
| <b>Transmission (%):</b><br>50                                        |
| <b>Type:</b><br>Mounted Imaging Filter                                |
| <b>Blocking Wavelength Range (nm):</b><br>400 - 700                   |
| <b>Mount Thickness (mm):</b><br>5.2 ±0.3                              |
| <b>Note:</b><br>AR Coating: MgF <sub>2</sub>                          |
| <b>Coating Specification:</b><br>R <sub>avg</sub> ≤1.75% @400 - 700nm |
| <b>Mount Diameter (mm):</b><br>39.0 ±0.3                              |
| <b>Mount Thickness Including Threads (mm):</b><br>6.5                 |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>REACH 201:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |

---