

0.3 OD M49.0 x 0.75, Mounted Absorptive ND Filter



Stock **#54-729** 3-5 DAYS

- 1 +

A\$68.80

ADD TO CART

Qty 1-9
A\$68.80
Qty 10+
A\$63.20
Volume Pricing
Request Quote

Get Product Downloads

Optical Density OD (Average):
0.3

Clear Aperture CA (mm):
45.0

Filter Thread:
M49 x0.75

Substrate: ☐ ND Filter Glass

Thickness with Mount (mm): 5.00
Surface Quality: 80-50
Transmission (%): 50
Type: Mounted Imaging Filter
Blocking Wavelength Range (nm): 400 - 700
Mount Thickness (mm): 3.8 ±0.1
Note: AR Coating: MgF ₂
Coating Specification: R _{avg} ≤1.75% @400 - 700nm
Mount Diameter (mm): 51.0 +0/-0.2
Mount Thickness Including Threads (mm): 6.3

Regulatory Compliance

RoHS: Exempt
Certificate of Conformance: View