

0.5° Diffusing Angle 50mm Dia., Fused Silica Holographic Diffuser



Holographic UV Diffusers

Stock **#48-513** 3-5 DAYS

⊖ 1 ⊕

A\$1,144.00

ADD TO CART

Qty 1+
A\$1,144.00

Volume Pricing
Request Quote

Get Product Downloads

Angle Tolerance (°): ±0.5
Diffusing Angle (°): 0.5 (FWHM)
Clear Aperture CA (mm): 45.7 ±0.1
Diameter (mm): 50.00 ±0.1
Operating Temperature (°C): -40 to +170

Substrate: 
[Fused Silica](#) (Corning 7980)

Transmission (%):
Typical: 90

Type:
Holographic Diffuser

Wavelength Range (nm):
400 - 700

Construction:
Mounted

Mount Thickness (mm):
4.7 ±0.1

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)

Reach 233:
[Compliant](#)