

TECHSPEC® 0.6 OD 25mm Dia., NIR ND Filter



Near-IR (NIR) Neutral Density (ND) Filters

Stock **#49-069** 3-5 DAYS

- 1 +

A\$166.40

ADD TO CART

Qty 1-5

A\$166.40

Qty 6+

A\$133.12

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
25.00 +0.0/-0.2

Optical Density OD (Average):
0.6

Substrate: ☐
[Fused Silica](#) (Coming 7980)

Coating: Metallic Based ND
Surface Quality: 40-20
Thickness (mm): 3.00
Thickness Tolerance (mm): ±0.10
Transmission (%): 25.00
Type: Neutral Density Filter
Blocking Wavelength Range (nm): 700 - 1100
Clear Aperture (%): 80
Transmitted Wavefront, P-V: λ/4
Optical Density Tolerance (%): ±10
Parallelism (arcsec): <5

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant