


0.9 OD 50mm Sq, Absorptive ND Filter

See More by [Hoya](#)



Stock **#46-221** 3-5 DAYS

- 1 +

A\$152.00

ADD TO CART

Qty 1-10
A\$152.00
Qty 11+
A\$134.40
Volume Pricing
Request Quote

Get Product Downloads



Dimensions (mm):
50.0 x 50.0

Optical Density OD (Average):
0.9 ±0.1

Glass/Filter Number: Hoya ND-13
Substrate: ☐ ND Filter Glass
Length (mm): 50.00
Coating: Uncoated
Index of Refraction n_d: 1.51
Surface Quality: 80-50
Transformation Temperature (°C): 535
Thickness (mm): 2.50
Thickness Tolerance (mm): ±0.5
Transmission (%): 12.5 (average)
Type: Neutral Density Filter
Width (mm): 50.00
Blocking Wavelength Range (nm): 400 - 700
Dimensional Tolerance (mm): ±0.2
Parallelism (mm): <0.02

Regulatory Compliance

RoHS 2015: Compliant
REACH 201: Compliant
Certificate of Conformance: View