

## 0.9 OD M58.0 x 0.75, Mounted Absorptive ND Filter



Stock **#54-743** CLEARANCE 3-5 DAYS

⊖ 1 ⊕

A\$62.32

ADD TO CART

Qty 1+

A\$62.32

Volume Pricing

[Request Quote](#)

Get Product Downloads

**Optical Density OD (Average):**  
0.9

**Clear Aperture CA (mm):**  
54.0

**Filter Thread:**  
M58 x0.75

**Substrate:** ☐  
ND Filter Glass

**Thickness with Mount (mm):**  
5.00

|                                                                       |
|-----------------------------------------------------------------------|
| <b>Surface Quality:</b><br>80-50                                      |
| <b>Transmission (%):</b><br>12.5                                      |
| <b>Type:</b><br>Mounted Imaging Filter                                |
| <b>Blocking Wavelength Range (nm):</b><br>400 - 700                   |
| <b>Mount Thickness (mm):</b><br>3.8 ±0.1                              |
| <b>Note:</b><br>AR Coating: MgF <sub>2</sub>                          |
| <b>Coating Specification:</b><br>R <sub>avg</sub> ≤1.75% @400 - 700nm |
| <b>Mount Diameter (mm):</b><br>60.0 +0/-0.2                           |
| <b>Mount Thickness Including Threads (mm):</b><br>6.3                 |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS:</b><br><a href="#">Exempt</a>                     |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |