

1 x 60° Diffusing Angle 2" x 2" Unmounted



Stock #48-003 3-5 DAYS

-

1

+

A\$388.00

ADD TO CART

Qty 1-5

A\$388.00

Qty 6+

A\$330.00

Volume Pricing

[Request Quote](#)

Get Product Downloads

Angle Tolerance (°):
±0.5 x ±6

Diffusing Angle (°):
1 x 60 (FWHM)

Dimensional Tolerance (mm):
±0.5

Dimensions (inches):
2 x 2

Dimensions (mm): 50.80 x 50.80
Operating Temperature (°C): -30 to +100 (Maximum of 240 Hours)
Substrate: ☐ Polycarbonate
Thickness (mm): 0.78
Transmission (%): >85
Type: Holographic Diffuser
Wavelength Range (nm): 400 - 700
Width (mm): 50.80
Construction: Unmounted
Damage Threshold, By Design: ☐ 0.22 J/cm ² @ 1064nm, 10ns (typical)
Length (mm): 50.80

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant