

10 x 10mm 120 Grit Ground Glass Diffuser



Stock #83-083

3-5 DAYS

-

1

+

A\$28.40

ADD TO CART

Qty 1-10

A\$28.40

Qty 11+

A\$24.40

Volume Pricing

[Request Quote](#)

Get Product Downloads

Coating:

Uncoated

Dimensional Tolerance (mm):

±0.25

Dimensions (mm):

10.00 x 10.00

Edges:

Cut Edges

Grit: 120
Substrate: Float Glass
Thickness (mm): 1.60
Type: Ground Glass Diffuser
Wavelength Range (nm): 350 - 2000
Width (mm): 10.00
Note: Sandblasted on first surface
Length (mm): 10.00

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant
