

[All Products](#) / [Optics](#) / [Optical Mirrors](#) / [Flat Mirrors](#) / [Float Glass](#) / [First Surface Mirrors](#)

[See all 150 Products in Family](#)

TECHSPEC® 10 x 14mm Enhanced Aluminum, 4-6λ Mirror



Stock **#48-449** 3-5 DAYS

- 1 +

A\$38.40

ADD TO CART

Qty 1-5
A\$38.40
Qty 6+
A\$29.60
Volume Pricing
Request Quote

Get Product Downloads

Surface Flatness (P-V):
4 - 6λ

Substrate: ☐
Float Glass

Surface Quality:
60-40

Dimensions (mm):
10.0 x 14.0

Dimensional Tolerance (mm): ±0.25
Coating Specification: R _{avg} ≥95% @450 - 650nm @45°
Coating: Enhanced Aluminum (450-650nm)
Coating Type: Metal
Clear Aperture CA (mm): 9.00 x 13.00
Edges: Seamed, 0.5mm Maximum Edge Chip
Thickness (mm): 2.00
Type: Flat Mirror
Wavelength Range (nm): 450 - 650
Length (mm): 14.00
Width (mm): 10.00
Damage Threshold, By Design: ☐ 0.2 J/cm ² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant