

100 x 100mm Right-Handed Circular Polarizing Film (CP42HER)



Stock **#88-093** CLEARANCE 3-5 DAYS

- 1 +

A\$55.92

ADD TO CART

Qty 1+
A\$55.92

Volume Pricing
Request Quote

Get Product Downloads

Substrate: [Polymer Film CP42HER](#)

Length (mm):
100.00

Operating Temperature (°C):
-40 to +80

Dimensions (mm):
100.0 x 100.0

Thickness (mm):
0.27 ±0.04

Transmission (%) : 42.00
Type : Right-Handed Circular Polarizer
Dimensional Tolerance (mm) : +0.0/-1.0
Construction : Polarizing Film
Wavelength Range (nm) : 400 - 700
Polarization Efficiency (%) : >99.90
Heat Resistance (°C x Hours) : 80 x 500
Width (mm) : 100.00
#Sorting : 24.00

Regulatory Compliance

RoHS 2015 : Compliant
Certificate of Conformance : View
Reach 235 : Contains SVHC(s)