

10mm Aperture, 18mm FL VIS/NIR Fiber Refocusing Assembly



Fiber Refocusing Assembly

Stock **#88-182** 3-5 DAYS



1



A\$272.00

ADD TO CART

Qty 1-10

A\$272.00

Qty 11+

A\$240.00

Volume Pricing

[Request Quote](#)

Get Product Downloads

Diameter (mm):
15.88

Substrate:
[N-BK7](#)

Type:
Refocusing Assembly

Wavelength Range (nm):

350 - 2200
Aperture Size: 10.0
Focal Length FL (mm): 18.00
Housing Material: Anodized Aluminum
Length (mm): 16.38
Note: Compatible with #88-180 , #88-181 , #88-190 , & #88-191 Fiber Collimators
Operating Temperature (°C): -40 to 100

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View