

5mm Max. Aperture, Iris Diaphragm



Stock #54-352 3-5 DAYS

-

1

+

A\$107.20

ADD TO CART

Qty 1-4
A\$107.20
Qty 5+
A\$94.40
Volume Pricing
Request Quote

Get Product Downloads

Type:
Unmounted

Minimum Aperture (mm):
0.6

Maximum Aperture (mm):
5.0

Outer Diameter (mm):
10.0

Construction: Brass Housing, Blue Tempered Steel Leaves
Lever Diameter (mm): 1.50
Lever Length (mm): 7.50
Number of Leaves: 6.00
Thickness (mm): 4.50

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View
Reach 240: Contains SVHC(s)

