

10X Mitutoyo Plan Apo HR Infinity Corrected Objective

See More by [Mitutoyo](#)



Stock #58-236 3-5 DAYS

− 1 +

A\$13,665.60

ADD TO CART

Qty 1+
A\$13,665.60

Volume Pricing
Request Quote

Get Product Downloads

Compatible Cover Glass Thickness (mm):
N/A

Horizontal Field of View, 1/2" Sensor:
0.64mm

Horizontal Field of View, 2/3" Sensor:
0.88mm

Focal Length FL (mm):
20.00

Model Number: 378-788-4
Length excluding Threads (mm): 80.00
Magnification: 10X
Maximum Diameter (mm): 34
Maximum Sensor Format: 2/3"
Numerical Aperture NA: 0.42
Mounting Threads: M26 x36 TPI
Compatible Tube Lens Focal Length (mm): Focal Length: 200mm
Type: Microscope Objective
Resolving Power (μm): 0.6
Depth of Field (μm): 1.55
Field of View, 24 Diameter Field Eyepiece (mm): 2.4
Field of View, 18 Diameter Field Eyepiece (mm): 1.8
Operating Temperature (°C): +5 to +40
Operating Humidity: 20 - 80%
Working Distance (mm): 15.0
Weight (g): 460.00
Wavelength Range (nm): 435 - 655
Style: Infinity Corrected
Manufacturer: Mtutoyo
Parfocal Length (mm): 95
Immersion Liquid: N/A
Exit Pupil Diameter (mm): 16.80

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View
Reach 240: Contains SVHC(s)