

120 MHz Fiber Coupled Optical Reciever Module



Stock **#87-324** 3-5 DAYS

-

1

+

A\$416.00

ADD TO CART

Qty 1+
A\$416.00

Volume Pricing
Request Quote

Get Product Downloads

Sensitivity (dBm):
-42

Wavelength Range (nm):
1310 - 1550

Connector:
FC/PC

Dynamic Range (dB):
25.00

Fiber Diameter (µm):
50/125/245/900

Regulatory Compliance

RoHS:
Not Compliant

Certificate of Conformance:
[View](#)
