

TECHSPEC® 12.5" Diameter x 75" FL Enhanced Aluminum, Parabolic Mirror



Stock #32-276-533 3-5 DAYS

⊖ 1 ⊕ **A\$5,224.00**

ADD TO CART

Qty 1-2
A\$5,224.00
Qty 3+
A\$4,440.00
Volume Pricing
Request Quote

Get Product Downloads

Substrate: ☐ BOROFLOAT®☒ SUPREMAX®

Focal Length Tolerance (%): ±1.5

Surface Quality: 60-40

Surface Accuracy: λ/8

Diameter (inches): 12.5 +0.06/-0
Diameter (mm): 317.50 +1.5/-0
Effective Focal Length EFL (inches): 75.0
Effective Focal Length EFL (mm): 1,905.00
Radius of Curvature (mm): 3,810.00
Aperture (f/#): f/6
Coating: Enhanced Aluminum (450-650nm)
Coating Specification: R_{avg} >95% @ 450 - 650nm
Coating Type: Metal
Back Surface: Ground
Clear Aperture CA (mm): 286
Edge Thickness ET (inches): 2.13
Edge Thickness ET (mm): 54.10
Type: Parabolic Mirror
Wavelength Range (µm): 0.45 - 0.65
Wavelength Range (nm): 450 - 650
Damage Threshold, Reference: 0.2 J/cm² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant