

TECHSPEC[®] 12.5/12.7mm Optic Dia., Kinematic Mount, 2-Screws



12.5/12.7mm Diameter Kinematic Mount, 2-Screws, #58-850

Stock #58-850 3-5 DAYS

-

1

+

A\$137.60

ADD TO CART

Qty 1-4

A\$137.60

Qty 5+

A\$123.84

Volume Pricing

[Request Quote](#)

Get Product Downloads

Type:
Adjustable - Tip-Tilt

Type of Optics:
Circular

Size of Compatible Optics (mm):
12.5 - 12.7

Number of Adjustment Screws:

2
Clear Aperture CA (mm): 10.9
Travel (mm): No Z-Axis Translation
Construction: Aluminum Plates, Stainless Steel Screws, and Brass Thread Bushings
Angle Tolerance (°): 0.4 per 0.25mm turn
Fine Tilt Angle (°): ±5
Fine Tip Angle (°): ±5
Sensitivity per 1° Knob Rotation (arcsec): 4
Thermal Stability (μrad): <5
Adjustment Screw Pitch (mm): 0.25
Compatible Post: M4 x0.7, 8-32
Min. Thickness of Compatible Optics (mm): 1.8
Pointing Stability (μrad): 1.3

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View
