

12mm Dia. x 48mm FL, Commercial Grade, Plano-Convex Lens



Stock **#23-074** CLEARANCE 3-5 DAYS

[Other Coating Options](#)

-

1

+

A\$31.92

ADD TO CART

Qty 1+
A\$31.92

Volume Pricing
Request Quote

Get Product Downloads

Diameter (mm):
12.00 +0.00/-0.10

Effective Focal Length EFL (mm):
48.00

Back Focal Length BFL (mm):
46.69

Coating:
Uncoated

Substrate:

[N-BK7](#)

Focal Length Tolerance (%): ±1
Centering (arcmin): 6.00
Center Thickness CT (mm): 2.00
Edge Thickness ET (mm): 1.26
Radius R₁ (mm): 24.81
Clear Aperture CA (mm): ≥10.2
f/#: 4.00
Numerical Aperture NA: 0.13
Type: Plano-Convex Lens

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View