

8mm Max. Aperture, Burnished Steel Leaves Iris Diaphragm



Standard Series

Stock #57-580 3-5 DAYS



1



A\$112.00

ADD TO CART

Qty 1-4

A\$112.00

Qty 5+

A\$98.72

Volume Pricing

[Request Quote](#)

Get Product Downloads

Type:

Unmounted

Minimum Aperture (mm):

1.0, Typical

Maximum Aperture (mm):

8.0

Outer Diameter (mm):

14.8
Construction: Anodized Aluminum Alloy, Burnished Spring Steel Leaves
Lever Diameter (mm): 1.50
Lever Length (mm): 6.00
Number of Leaves: 9
Thickness (mm): 4.50

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant