

1.5 OD, 25mm Dia., IR Neutral Density Filter



Infrared (IR) Neutral Density (ND) Filters

Stock #87-200 3-5 DAYS



1



A\$614.40

ADD TO CART

Qty 1-10

A\$614.40

Qty 11+

A\$551.84

Volume Pricing

[Request Quote](#)

Get Product Downloads

Diameter (mm):

25.00 ±0.2

Optical Density OD (Average):

1.5

Substrate: ☐

Germanium (Ge)

Coating:

|                                                         |
|---------------------------------------------------------|
| Metallic Based ND                                       |
| <b>Surface Quality:</b><br>80-50                        |
| <b>Thickness (mm):</b><br>1.00 ±0.2                     |
| <b>Transmission (%):</b><br>3.2                         |
| <b>Transmission Tolerance (%):</b><br>±0.7              |
| <b>Type:</b><br>Neutral Density Filter                  |
| <b>Blocking Wavelength Range (nm):</b><br>2000 - 14,000 |
| <b>Parallelism (arcmin):</b><br><10                     |
| <b>Clear Aperture (%):</b><br>90                        |
| <b>Wavelength Range (µm):</b><br>2 - 14                 |
| <b>Surface Flatness (P-V):</b><br>3 - 5λ                |

### Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 235:</b><br><a href="#">Compliant</a>             |