

TECHSPEC[®] 15.0mm Dia. x 45.0mm FL, VIS-EXT, Inked, Plano-Convex Lens



Stock **#88-699-INK** 10-15 DAYS
[Other Coating Options](#)

-

1

+

A\$86.40

ADD TO CART

Qty 1-9
A\$86.40
Qty 10+
A\$77.60
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
15.00 ±0.025

Effective Focal Length EFL (mm):
45.00 @ 587.6nm

Back Focal Length BFL (mm): 43.35
Coating: VIS-EXT (350-700nm)
Coating Specification: R _{avg} <0.5% @ 350 - 700nm
Substrate: ☐ N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 2.50 ±0.10
Edge Thickness ET (mm): 1.26
Radius R₁ (mm): 23.26
Clear Aperture CA (mm): 14
f/#: 3
Numerical Aperture NA: 0.17
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 350 - 700
Damage Threshold, By Design: ☐ 5 J/cm ² @ 532nm, 10ns

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View