

TECHSPEC®

15.0mm Dia. x 60.0mm FL, VIS-EXT Coated Plano-Convex Lens



Stock **#88-700** 3-5 DAYS

[Other Coating Options](#)



1



A\$70.40

ADD TO CART

Qty 1-9
A\$70.40
Qty 10+
A\$63.20
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
15.00 +0.0/-0.025

Effective Focal Length EFL (mm):
60.00 @ 550nm

Back Focal Length BFL (mm): 58.65
Coating: VIS-EXT (350-700nm)
Coating Specification: R _{avg} <0.5% @ 350 - 700nm
Substrate: ☐ N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 2.05 ±0.10
Edge Thickness ET (mm): 1.13
Radius R₁ (mm): 31.11
Clear Aperture CA (mm): 14
f#: 4
Numerical Aperture NA: 0.13
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 350 - 700
Damage Threshold, By Design: ☐ 5 J/cm ² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant