

TECHSPEC® 16.25" Diameter x 80" FL Uncoated, Parabolic Mirror



Stock #32-725-000 3-5 DAYS

- 1 + **A\$11,188.80**

ADD TO CART

Qty 1-2
A\$11,188.80
Qty 3+
A\$9,510.40
Volume Pricing
Request Quote

Get Product Downloads

Substrate:
[BOROFLOAT®](#)[SUPREMAX®](#)

Focal Length Tolerance (%):
±1.5

Surface Quality:
60-40

Surface Accuracy:
λ/8

Diameter (inches): 16.25 +0.06/-0
Diameter (mm): 412.80 +1.5/-0
Effective Focal Length EFL (inches): 80.0
Effective Focal Length EFL (mm): 2,032.00
Radius of Curvature (mm): 4,064.00
Aperture (f/#): f/4.9
Coating: Uncoated
Coating Type: Uncoated
Back Surface: Ground
Clear Aperture CA (mm): 372
Edge Thickness ET (inches): 3.25
Edge Thickness ET (mm): 82.60
Type: Parabolic Mirror

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View