

16mm FL SWIR Series Fixed Focal Length Lens



Stock #83-817 3-5 DAYS

- 1 + **A\$3,368.00**

ADD TO CART

Qty 1+
A\$3,368.00

Volume Pricing
Request Quote

Get Product Downloads

Field of View @ Min Working Distance (mm): 235
Iris Option: Variable
Length (mm): 52.90
Filter Thread: M34.5 x0.50
Maximum Diameter (mm): 42.0

Weight (g): 150
Horizontal Field of View, 1" Sensor: 44.3°
Maximum Image Circle (mm): 16.00
Type: Fixed Focal Length Lens
Focal Length FL (mm): 16.00
Maximum Sensor Format: 1"
Working Distance (mm): 300 - ∞
Mount: C-Mount
Aperture (f/#): f/1.4 - f/16
Distortion (%): <1.0
Lens Wavelength Range: SWIR

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View
Reach 240: Contains SVHC(s)
