

193nm CWL, 15nm FWHM, 50mm Mounted Diameter



Stock #67-866 3-5 DAYS

-

1

+

A\$873.60

ADD TO CART

Qty 1-9
A\$873.60
Qty 10+
A\$786.08
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
50.00 +0.00/-0.25

Angle of Incidence (°):
0

Optical Density OD (Average):
≥4.0

Clear Aperture CA (mm):

45.0
Center Wavelength CWL (nm): 193.00 ±3.5
Center Wavelength CWL Tolerance (nm): ±3.5
Full Width-Half Max FWHM (nm): 15.00 ±3
Full Width-Half Max FWHM Tolerance (nm): ±3
Minimum Transmission (%): >12
Operating Temperature (°C): -50 to +50
Coating: Traditional Coated
Surface Quality: 80-50
Type: Bandpass Filter
Typical Applications: ArF Laser Line
Blocking Wavelength Range (nm): 200 - 10000
Construction: Mounted in Black Anodized Ring
Mount Thickness (mm): 3.5

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant