

# 1" x 1" (30 lp/mm), Ronchi Ruling



Stock #66-347 3-5 DAYS

-

1

+

A\$347.20

ADD TO CART

Qty 1-4

A\$347.20

Qty 5+

A\$330.88

Volume Pricing

[Request Quote](#)

Get Product Downloads

**Coating:**  
Vacuum Deposited Chrome, OD >3.0

**Dimensional Tolerance (inches):**  
±0.02

**Frequency (lp/mm):**  
30

**Substrate:**  
Float Glass

|                                                       |
|-------------------------------------------------------|
| <b>Optical Density OD (Average):</b><br>3.00          |
| <b>Dimensions (inches):</b><br>1 x 1                  |
| <b>Surface Quality:</b><br>60-40                      |
| <b>Thickness (mm):</b><br>1.50                        |
| <b>Type:</b><br>Metric                                |
| <b>Dimensional Tolerance (mm):</b><br>± 0.02          |
| <b>Line to Line Parallelism (arcsec):</b><br>≤2       |
| <b>Parallelism of Pattern to Substrate (°):</b><br>±1 |
| <b>Surface Flatness (P-V):</b><br>1λ                  |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Reach 209:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |