

20 x 27mm, 30R/70T, Plate Beamsplitter



Stock **#46-693** 3-5 DAYS

-

1

+

A\$78.40

ADD TO CART

Qty 1-9
A\$78.40
Qty 10+
A\$56.00
Volume Pricing
Request Quote

Get Product Downloads



Coating Specification:
Surface 1: Dielectric, ±5% R/T @ 550nm
Surface 2: Uncoated

Construction:
Plate

Dimensional Tolerance (mm):
±0.38

Dimensions (mm): 20.0 x 27.0
Edges: Cut
Reflection/Transmission Ratio (R/T): 30/70
Substrate: ☐ Float Glass
Surface Flatness (P-V): 4 - 6λ
Surface Quality: 80-50
Thickness (mm): 1.00
Type: Standard Beamsplitter
Wavelength Range (nm): 400 - 700

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant