

200µm Aperture Diameter, Unmounted, Precision Pinhole



Unmounted Precision Pinhole

Stock #39-728 3-5 DAYS



1



A\$104.00

ADD TO CART

Qty 1-5

A\$104.00

Qty 6+

A\$92.16

Volume Pricing

[Request Quote](#)

Get Product Downloads

Type:

Unmounted

Outer Diameter (mm):

9.5

Construction:

Stainless Steel

Fixed Aperture Diameter (µm):

200
Thickness (mm): 0.03 Nominal
Aperture Tolerance (µm): ±5
Aperture Centration (µm): ±50

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant
