

TECHSPEC[®] 20mm N-SF11 MgF₂ Coated Equilateral Prism



Equilateral Prisms

Stock #49-434 3-5 DAYS



1



A\$204.80

ADD TO CART

Qty 1-5

A\$204.80

Qty 6+

A\$184.32

Volume Pricing

[Request Quote](#)

Get Product Downloads

Coating:
MgF₂ (400-700nm)

Length of Face (mm):
20.00

Substrate: ☐
[N-SF11](#)

Length (mm):

20.00
Surface Quality: 40-20
Type: Equilateral Prism
Dimensional Tolerance (mm): ±0.1
Angle Tolerance (arcmin): ±2
Image Orientation: Dispersion
Coating Specification: R _{avg} ≤1.75% @400 - 700nm
Wavelength Range (nm): 400 - 700
Surface Flatness (P-V): λ/4

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View
