

TECHSPEC® 20mm Protected Gold Coated, N-BK7 Right Angle Mirror



Stock **#47-029** 3-5 DAYS

- 1 + **A\$212.00**

ADD TO CART

Qty 1-5
A\$212.00
Qty 6+
A\$169.60
Volume Pricing
Request Quote

Get Product Downloads



Surface Flatness (P-V):
λ/8

Substrate:
[N-BK7](#)

Surface Quality:
40-20

Length of Legs (mm):

20.00
Dimensional Tolerance (mm): ±0.1
Coating Specification: R _{avg} >96% @ 700 - 2000nm R _{avg} >96% @ 2000 - 10,000nm
Coating: Protected Gold (700-10000nm)
Coating Type: Metal
Angle Tolerance (arcmin): ±2
Bevel: Protective bevel as needed
Clear Aperture CA (mm): 25.45 x 18.00
Length of Hypotenuse (mm): 28.30
Type: Right Angle Mirror
Wavelength Range (µm): 0.7 - 10
Wavelength Range (nm): 700 - 10000
Damage Threshold, Reference: ☐ 0.8 J/cm² @ 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant
