

20X Objective, Nikon CFI Super Fluor

See More by [Nikon](#)



Stock #88-376 [CONTACT US](#)

⊖ 1 ⊕

A\$10,108.80

ADD TO CART

Qty 1+

A\$10,108.80

Volume Pricing

[Request Quote](#)

Get Product Downloads

Compatible Cover Glass Thickness (mm):
0.17

Field of View (mm):
1.10

Horizontal Field of View, 1/2" Sensor:
0.32mm

Horizontal Field of View, 2/3" Sensor:
0.44mm

Model Number:
MRF00201

Length (mm): 58.90
Length excluding Threads (mm): 58.90
Magnification: 20X
Maximum Diameter (mm): 33.5
Maximum Sensor Format: 2/3"
Numerical Aperture NA: 0.75
Mounting Threads: M25 x 0.75
Compatible Tube Lens Focal Length (mm): Focal Length: 200mm
Type: Microscope Objective
Working Distance (mm): 1.0
Weight (g): 198.00
Style: Infinity Corrected
Manufacturer: Nikon
Field Number (mm): 22
Parfocal Length (mm): 59.9
Immersion Liquid: N/A

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View