

220mm Dia x 440mm FL Cold Mirror Coated, Ellipsoidal Reflector



Precision Ellipsoidal Reflectors

Stock #68-803 3-5 DAYS

-

1

+

A\$1,987.20

ADD TO CART

Qty 1-10
A\$1,987.20
Qty 11+
A\$1,754.40
Volume Pricing
Request Quote

Get Product Downloads

Substrate:
[BOROFLOAT®](#)

Coating:
Cold Mirror, 0°

Coating Type:
Metal

Center Hole Diameter (mm):

60.0
Height (mm): 91.0
Inner Diameter (mm): 210
Outer Diameter (mm): 220.00 +0.0/-0.5
Type: Specialty Mirror
Distance to Focal Point f_1 (mm) : 40
Distance to Focal Point f_2 (mm): 440

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View
