

23" Single Branch Semi-Rigid Light Guide



Stock #54-210 3-5 DAYS

-

1

+

A\$353.60

ADD TO CART

Qty 1+
A\$353.60

Volume Pricing
Request Quote

Get Product Downloads

Acceptance Angle (°):
68.00

Minimum Bend Radius (mm):
101.6

Fiber Bundle Diameter (inches):
0.188

Length (inches):
23.00

Numerical Aperture NA:
0.55

Operating Temperature (°C): -40 to +107
Fiber Diameter (µm): 50.00
Type: Single Branch
Length Tolerance (inches): ±0.5
Packing Fraction (%): 82.00
Index of Refraction n_d - Core: 1.581
Index of Refraction n_d - Cladding: 1.487
Transmission Loss: 6% per foot at 600nm
Type of Illumination: Fiber Optic Light Guide
Compatible Light Guide Adapter: SX: #38-946
Geometry: Spot Light

Regulatory Compliance

Reach 174: Compliant
RoHS: Not Compliant
Certificate of Conformance: View
