

TECHSPEC® 2.5 OD 12.5mm Diameter UV-VIS ND Filter



Stock #48-624 3-5 DAYS

-

1

+

A\$144.00

ADD TO CART

Qty 1-5

A\$144.00

Qty 6+

A\$115.04

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):  
12.50 +0.00/-0.20

Optical Density OD (Average):  
2.5

Substrate: 

Fused Silica (Corning 7980)

Coating:

|                                                     |
|-----------------------------------------------------|
| Metallic Based ND                                   |
| <b>Surface Quality:</b><br>40-20                    |
| <b>Thickness (mm):</b><br>1.50                      |
| <b>Thickness Tolerance (mm):</b><br>±0.10           |
| <b>Transmission (%):</b><br>0.3                     |
| <b>Type:</b><br>Neutral Density Filter              |
| <b>Blocking Wavelength Range (nm):</b><br>250 - 700 |
| <b>Clear Aperture (%):</b><br>80.00                 |
| <b>Transmitted Wavefront, P-V:</b><br>λ/4           |
| <b>Optical Density Tolerance (%):</b><br>±10        |
| <b>Parallelism (arcsec):</b><br><5                  |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 235:</b><br><a href="#">Compliant</a>             |