

TECHSPEC[®] 25 x 25mm Protected Gold, λ/4 Mirror



Stock #45-335 3-5 DAYS

-

1

+

A\$144.00

ADD TO CART

Qty 1-5

A\$144.00

Qty 6+

A\$115.20

Volume Pricing

[Request Quote](#)

Get Product Downloads



Surface Flatness (P-V):
λ/4

Substrate: 
BOROFLOAT[®]

Back Surface:
Commercial Polish

Surface Quality:

60-40
Dimensions (mm): 25.0 x 25.0
Dimensional Tolerance (mm): ±0.25
Coating Specification: R _{avg} >96% @ 700 - 2000nm R _{avg} >96% @ 2000 - 10,000nm
Coating: Protected Gold (700-10000nm)
Coating Type: Metal
Bevel: Protective bevel as needed
Clear Aperture (%): 85
Edges: Fine Ground
Thickness (mm): 6.00 ±0.25
Type: Flat Mirror
Wavelength Range (µm): 0.7 - 10
Wavelength Range (nm): 700 - 10000
Length (mm): 25.00
Width (mm): 25.00
Damage Threshold, Reference: ☐ 0.8 J/cm² @ 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant