


TECHSPEC[®] 25mm 532nm, Laser Line Non-Polarizing Cube Beamsplitter



Laser Line Non-Polarizing Cube Beamsplitters



Stock #35-960 3-5 DAYS

- 1 +

A\$441.60

ADD TO CART

Qty 1-5

A\$441.60

Qty 6+

A\$353.60

Volume Pricing

[Request Quote](#)

Get Product Downloads

Beam Deviation (arcmin):
±2

Bevel:
Protective as needed

Clear Aperture (%):

90
Coating Specification: <0.25% Reflection on Entrance and Exit Faces
Construction: Cube
Design Wavelength DWL (nm): 532
Dimensions (mm): 25.0 x 25.0 x 25.0 ±0.1
Reflection/Transmission Tolerance (%): ±5
Substrate:  N-BK7
Surface Flatness (P-V): λ/8
Surface Quality: 40-20
Transmission (%): <45% ±5% @ DWL
Type: Non-Polarizing Beamsplitter
[Ts-Tp]: <3% @ DWL
Power (fringes) @ 632.8nm: 1.50
Irregularity (fringes) @ 632.8nm: 0.25

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View