

TECHSPEC® 25mm Dia x 25mm FL MgF₂ Coated, Illumination Grade PCX Cylinder Lens



Stock #48-357

3-5 DAYS

-

1

+

A\$126.40

ADD TO CART

Qty 1-5

A\$126.40

Qty 6+

A\$100.80

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
25.00

Effective Focal Length EFL (mm):
25.00

Substrate:

N-BK7

f/#:

1
Numerical Aperture NA: 0.5
Coating: MgF ₂ (400-700nm)
Type: Cylinder Lens, Plano-Convex
Wavelength Range (nm): 400 - 700
Back Focal Length BFL (mm): 17.74
Center Thickness CT (mm): 11.03
Center Thickness Tolerance (mm): ±0.1
Coating Specification: R _{avg} ≤1.75% @400 - 700nm
Dimensional Tolerance (mm): +0.0/-0.2
Edge Thickness ET (mm): 1.49
Focal Length Tolerance (%): ±3
Radius R₁ (mm): 12.96
Surface Quality: 60-40
Damage Threshold, By Design: ☐ 10 J/cm ² @532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant