

TECHSPEC[®] 25mm Dia x -25mm FL, Enhanced Aluminum, Convex Mirror



Convex Mirrors

Stock #87-667 3-5 DAYS



1



A\$82.40

ADD TO CART

Qty 1-5

A\$82.40

Qty 6+

A\$65.60

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
25.00

Focal Length FL (mm):
-25.00

Center Thickness CT (mm):
3.00

Clear Aperture (%) 90.00
Coating: Enhanced Aluminum (450-650nm)
Coating Specification: R_{avg} >95% @450 - 650nm
Coating Type: Metal
Dimensional Tolerance (mm): +0.0/-0.1
Edge Thickness ET (mm): 1.41
Focal Length Tolerance (%): ±2
Radius R (mm): 50.0
Substrate: N-BK7
Surface Accuracy: λ/2
Surface Quality: 60-40
Thickness Tolerance (mm): ±0.1
Type: Spherical Mirror
Wavelength Range (nm): 450 - 650

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant