

25mm Diameter UV Fused Silica Ground Glass Optical Diffuser



Stock **#49-157** 3-5 DAYS

- 1 +

A\$88.80

ADD TO CART

Qty 1-10
A\$88.80
Qty 11+
A\$71.20
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
25.00 ±0.25

Grit: ☐
220

Substrate: ☐
[Fused Silica](#) (Corning 7980)

Thickness (mm):

1.60

Type:
Ground Glass Diffuser

Wavelength Range (nm):
200 - 2200

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)

Reach 233:
[Compliant](#)