

TECHSPEC[®] 25mm Diameter x 25mm FL, Uncoated, Plastic Aspheric Lens



TECHSPEC[®] Plastic Aspheric Lenses

Stock #66-008 CLEARANCE 3-5 DAYS

[Other Coating Options](#)



1



A\$78.40

ADD TO CART

Qty 1-24

A\$78.40

Qty 25+

A\$56.00

Volume Pricing

[Request Quote](#)

Get Product Downloads

Diameter (mm):
25.00 ±0.1

Effective Focal Length EFL (mm):
25.00 @ 587.6nm

Numerical Aperture NA:
0.50

Back Focal Length BFL (mm): 20.52
Substrate:  Zeonex E48R
Aspheric Design Wavelength (nm): 587.6
Coating: Uncoated
Centering (arcmin): <5 (by design)
Surface Quality: 80-50
Clear Aperture CA (mm): 21.5
Edge Thickness ET (mm): 1.07
Center Thickness CT (mm): 7.40 ±0.20
f/#: 1.00
Bevel: Protective bevel as needed
Operating Temperature (°C): -30 to 70
Radius R₂ (mm): 152.34
Shape of Back Surface: Convex
Type: Aspheric Lens
Wavelength Range (nm): 350 - 1100
Conjugate Distance: Infinite

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View