

25mm Outer Dia., Zero Aperture, Burnished Steel Leaves



Zero Series

Stock **#57-587** 3-5 DAYS

- 1 + **A\$156.80**

ADD TO CART

Qty 1-4
A\$156.80
Qty 5+
A\$138.24
Volume Pricing
Request Quote

Get Product Downloads

Minimum Aperture (mm): 0.00
Maximum Aperture (mm): 12.0
Outer Diameter (mm): 25.0
Construction:

Anodized Aluminum Alloy, Burnished Leaves
Full Angular Range of Lever (°): 96.00
Lever Diameter (mm): 3.00
Lever Length (mm): 12.00
Lever Position (mm): 2.50
Number of Leaves: Two sets of 6
Operating Temperature (°C): <250
Pin Thread & Pitch: M1.4 x 0.30mm
Thickness (mm): 5.00

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant