

18mm Max. Aperture, AR Steel Leaves Iris Diaphragm



Standard Series

Stock #57-576 3-5 DAYS

- 1 + **A\$112.00**

ADD TO CART

Qty 1-4
A\$112.00
Qty 5+
A\$98.72
Volume Pricing
Request Quote

Get Product Downloads

Type:
Unmounted

Minimum Aperture (mm):
1.0, Typical

Maximum Aperture (mm):
18.0

Outer Diameter (mm):

28.0
Construction: Anodized Aluminum Alloy, Anti-Reflection (AR) Leaves
Lever Diameter (mm): 3.00
Lever Length (mm): 13.00
Number of Leaves: 12.00
Thickness (mm): 5.00

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant