



TECHSPEC®

2mm Aperture, 25mm L High NA, Hexagonal Light Pipe



N-BK7 Light Pipe Homogenizing Rods



Stock #48-582 3-5 DAYS

-

1

+

A\$204.00

ADD TO CART

Qty 1-5

A\$204.00

Qty 6+

A\$163.20

Volume Pricing

[Request Quote](#)

Get Product Downloads



Coating:

Uncoated

Substrate: ☐

N-BK7

Length (mm): 25.00
Surface Quality: 60-40
Type: Light Pipe
Entrance and Exit Aperture (mm): 2.00
Parallelism (arcmin): 5.00
Length Tolerance (mm): ±0.3
Aperture Tolerance (mm): ±0.10
Image Orientation: Light Homogenization
Light Source NA: High
Wavelength Range (nm): 350 - 2200
Surface Flatness (P-V): 1λ

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View