

2" x 2" (120 lp/mm), Ronchi Ruling



Stock #62-202 3-5 DAYS

- 1 + **A\$1,232.00**

ADD TO CART

Qty 1-4
A\$1,232.00
Qty 5+
A\$1,171.68
Volume Pricing
Request Quote

Get Product Downloads

Coating:
Vacuum Deposited Chrome, OD >3.0

Dimensional Tolerance (inches):
±0.02

Frequency (lp/mm):
120

Substrate:
Float Glass

Optical Density OD (Average): 3.00
Dimensions (inches): 2 x2
Surface Quality: 60-40
Thickness (mm): 1.50
Type: Metric
Dimensional Tolerance (mm): ± 0.02
Line to Line Parallelism (arcsec): ≤2
Parallelism of Pattern to Substrate (°): ±1
Surface Flatness (P-V): 1λ

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View