

20mm Max. Aperture, AR Steel Leaves Iris Diaphragm



Standard Series

Stock #57-577 3-5 DAYS



1



A\$137.60

ADD TO CART

Qty 1-4

A\$137.60

Qty 5+

A\$121.76

Volume Pricing

[Request Quote](#)

Get Product Downloads

Type:

Unmounted

Minimum Aperture (mm):

1.2, Typical

Maximum Aperture (mm):

20.0

Outer Diameter (mm):

30.0
Construction: Anodized Aluminum Alloy, Anti-Reflection (AR) Leaves
Lever Diameter (mm): 3.0
Lever Length (mm): 13.00
Number of Leaves: 12.00
Thickness (mm): 5.50

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant