

3.5mm FL, High Resolution, f/2.5, Micro Video Lens



Stock #88-588 3-5 DAYS

-

1

+

A\$118.40

ADD TO CART

Qty 1-49

A\$118.40

Qty 50+

A\$91.20

Volume Pricing

[Request Quote](#)

Get Product Downloads

Length (mm):
15.40

Maximum Diameter (mm):
15.0

Maximum Image Circle (mm):
6.50

Horizontal Field of View @ Max Sensor Format:
102.8

Resolution, On-Axis: 100 lp/mm @ 59.0% Contrast
Resolution, 0.7 Field: 100 lp/mm @ 46.0% Contrast
Resolution, Full Field: 100 lp/mm @ 28.0% Contrast
Note: High Resolution
TV Distortion (%): -58
Type: M12 Imaging Lens
Focal Length FL (mm): 3.50
Maximum Sensor Format: 1/2.8"
Working Distance (mm): 400 - ∞
Mount: M12 x 0.5 (S-Mount)
Aperture (f/#): f/2.5
IR Cut Filter: No
Lens Wavelength Range: VIS

Regulatory Compliance

Reach 205: Compliant
Certificate of Conformance: View