

3mm Dia. x 9mm FL, Commercial Grade, Plano-Convex Lens



Stock **#23-058** CLEARANCE 3-5 DAYS

[Other Coating Options](#)

- 1 +

A\$31.92

ADD TO CART

Qty 1+
A\$31.92

Volume Pricing
Request Quote

Get Product Downloads

Diameter (mm):
3.00 +0.00/-0.10

Effective Focal Length EFL (mm):
9.00

Back Focal Length BFL (mm):
8.01

Coating:
Uncoated

Substrate: [N-BK7](#)

Focal Length Tolerance (%): ±1
Centering (arcmin): 6.00
Center Thickness CT (mm): 1.50
Edge Thickness ET (mm): 1.25
Radius R₁ (mm): 4.65
Clear Aperture CA (mm): ≥2.55
f/#: 3.00
Numerical Aperture NA: 0.17
Type: Plano-Convex Lens

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View