

TECHSPEC®

400-700nm OD 0.3, M30.5 x 0.5 Absorptive ND Filter



Stock #66-717

CONTACT US

-

1

+

A\$124.80

ADD TO CART

Qty 1-9

A\$124.80

Qty 10+

A\$116.48

Volume Pricing

[Request Quote](#)

Get Product Downloads

Diameter (mm):

33.50

Optical Density OD (Average):

0.3

Clear Aperture CA (mm):

22.0

Filter Thread:

M30.5 x 0.50

Substrate: ND Filter Glass
Coating: Uncoated
Transmission (%): 50.00
Type: Neutral Density Filter
Stock No. of Unmounted Filter: #46-212
Mount Thickness (mm): 9.2
Wavelength Range (nm): 400 - 700

Regulatory Compliance

RoHS: Exempt
Certificate of Conformance: View