

4.4-11mm FL High Resolution Varifocal Lens



#68-665

Stock #68-665 3-5 DAYS



1



A\$856.00

ADD TO CART

Qty 1+

A\$856.00

Volume Pricing

[Request Quote](#)

Get Product Downloads

Field of View @ Min Working Distance (mm):
400 - 175

Length (mm):
56.50

Horizontal Field of View, 1/2" Sensor:
68.1° - 32.6°

Filter Thread:
M43 x0.75

Weight (g):
125.00

Note: Low Distortion
Type: Varifocal Lens
Diameter (mm): 45.00
Focal Length FL (mm): 4.40 - 11
Maximum Sensor Format: 1/1.8"
Working Distance (mm): 300 - ∞
Mount: C-Mount
Aperture (f/#): f/1.6 - f/16
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View
Reach 240: Contains SVHC(s)