

TECHSPEC® 45° Cold Mirror Mounted in C-Mount Cube



Stock **#62-642** [CONTACT US](#)

- 1 + **A\$448.00**

ADD TO CART

Qty 1+
A\$448.00

Volume Pricing
Request Quote

Get Product Downloads

Surface Quality:
80-50

Type:
Cold Mirror

Extension Length (mm):
38.0

Dimensional Tolerance (mm):
0.5

Type of Optics:
45° Cold Mirror

Coating Specification:
T_{avg} ≥90% @ 800 - 1200nm
R_{avg} ≥95% @ 425 - 650nm

Thread Type:
C-Mount (1" x32 TPI)

Coating:
Cold Mirror, 45°

Substrate: ☐
[BOROFLOAT®](#)

Filter Included:
[#64-449](#)

Regulatory Compliance

RoHS:
[Compliant](#)

Certificate of Conformance:
[View](#)
