

4mm Aperture VIS/NIR Fiber Optic Collimator, FC



4mm Aperture Fiber Optic Collimator, FC

Stock **#88-188** 3-5 DAYS



1



A\$288.00

ADD TO CART

Qty 1-10

A\$288.00

Qty 11+

A\$255.20

Volume Pricing

[Request Quote](#)

Get Product Downloads

Diameter (mm):
6.35

Substrate: ☐
[N-BK7](#)

Type:
Fiber Collimator

Wavelength Range (nm):

350 - 2200
Aperture Size: 4.0
Compatible Fiber NA: 0.22
Connector: FC
Fiber Diameter (µm): compatible up to 400
Focal Length FL (mm): 10.00
Housing Material: Stainless Steel
Length (mm): 19.70
Note: No Compatible Refocusing Assemblies
Operating Temperature (°C): -40 to 100

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View